




E-32

6 volt

For:	Prestolite Generator GAS-4136, Etc.
Replaces:	GEM-12
Crossover:	81-6200
Used On:	
Used With:	
Note:	Thicker brush than the E-32C
Lester Number:	4460-609

E-32




Dimensions: 6mm T X 13mm W X 16mm L

E-32C

6 volt

For:	Prestolite Generator GAS-4136, Etc.
Replaces:	GEM-13
Crossover:	81-6200-1
Used On:	
Used With:	
Note:	Thinner brush than the E-32
Lester Number:	4460-610

E-32C




Dimensions: 5mm T X 13mm W X 16mm L

E-39

For:	Generator
Replaces:	GAR-1012, GBJ-1012, GHA-1012, GWB-1012A
Crossover:	81-6201
Used On:	
Used With:	
Lester Number:	4460-601

E-39



Dimensions: 6.5mm T X 19.5mm W X 22mm L x 51mm LL

E-39C

For:	Generator
Replaces:	GAL-1168, GBM-1013A,B,C; GBJ-1013
Crossover:	81-6201
Used On:	
Used With:	
Note:	Thinner brush than the E-39; different shunt location
Lester Number:	4460-601

E-39C



Dimensions: 4.5mm T X 19.5mm W X 22mm L X 51mm LL

E-43

For:	Generator
Replaces:	GBW-1012A, GCJ-1012, GDF-1012, GFL-1012
Crossover:	81-6202, 3D-7504
Used On:	
Used With:	
Lester Number:	4460-602

E-43



Dimensions: 6mm T X 22.5mm W X 22.5mm L X 51mm LL


PRESTOLITE

Generator Brushes

St. Marys Carbon Company



E-57



Dimensions: 6.5mm T X 22.5mm W X 22.5mm L X 46mm LL

E-57

For:	Prestolite GGW Generator
Replaces:	GGU-1012
Crossover:	81-6204
Used On:	
Used With:	
Lester Number:	4460-605

E-59



Dimensions: 8mm T X 25.4mm W X 23mm L X 56mm LL

E-59

For:	Prestolite Generator
Replaces:	
Crossover:	81-6205
Used On:	
Used With:	
Lester Number:	4460-604

E-74



Dimensions: 6.5mm T X 22.5mm W X 22mm L X 45mm LL

E-74

For:	Prestolite Generator
Replaces:	MDL-12
Crossover:	81-6206
Used On:	
Used With:	
Lester Number:	4460-606